



## ER370 Transistor Megaphone with Siren

Thank you for your choice of Speco Technologies' **ER370** Megaphone. This unit is designed and manufactured to provide a mobile source for voice amplification. The durable, weatherproof construction ensures long-life, and the included carrying strap and built-in siren help make this an extremely versatile unit.

### OPERATING INSTRUCTIONS:

- 1) To begin operation, move the selector switch to "ON."
- 2) To make an announcement, hold the megaphone by the grip and slide the press-to-talk trigger switch back with your index finger.
- 3) Bring the microphone mouthpiece close to your mouth and speak with a loud voice.
- 4) Turn volume control dial on back of grip to adjust to the optimal sound level and to avoid feedback.
- 5) To use the siren, move the selector switch to "Siren" and pull trigger.
- 6) To stop using siren, move selector switch back to "ON" if you wish to make an announcement, or "OFF."
- 7) When not in use, the selector switch should be kept in the "OFF" position to minimize battery drain.

To insert batteries:

- 1) Open battery compartment on the back of unit.
- 2) Place four C-type batteries in each battery case, observing correct polarity.
- 3) Insert battery case with batteries into the compartment of the megaphone, and close cover.

NOTE: Remove batteries when the **ER370** is not in use for an extended period of time.

### SPECIFICATIONS:

- Output: 20W Maximum, 10W Rated
- Power Source: Type C (UM-2) x 8 or DC 12V
- Typical Battery Life: 15 hours (intermittent use)
- Optimal Operating Distance (max volume): 800'
- Siren Output Level: 105dB
- Dimensions: 9 1/8" (Cone) x 14 1/4" (Length)
- Weight (without batteries): 3 1/4 lbs.
- Weatherproof, impact-resistant construction



### WARRANTY INFORMATION:

We warranty this product to be free from any manufacturing or material defects for one (1) year from the date of purchase.

This warranty will not extend to any products which have been subjected to misuse, neglect, accident, or improper installation, used in violation of instructions furnished by us; or to units which have been repaired or altered outside of the factory. This limited warranty does not apply to broken cases, batteries, or other physically damaged parts. If a Speco Technologies product is purchased from an unauthorized distributor or other source, including RETAILERS, MAIL ORDER SELLERS and ONLINE SELLERS, it will not be honored or serviced under existing Speco Technologies warranty policy. Any sale of products by an unauthorized source or other manner not authorized by Speco Technologies will void the warranty on the applicable product.

Upon request by customer, Speco Technologies ("The Company") will, at customer's expense, repackage merchandise in new cartons, replace missing accessories, and return in resalable condition. Unless requested, the company will replace and return all merchandise in the packaging in which it was received. This warranty is in lieu of all expressed warranties, expressed or implied, and of all obligations or liability on our part, and we neither assume nor authorize any representative or other person to assume for us any obligation or liability. In no event shall we be liable for incidental or consequential damages arising from the use of the product, or for any delay in the use of this product due to causes beyond our control. Some states do not allow limitations of how long an implied warranty lasts and/or do not allow the exclusion or limitation of consequential damages. The above limitations on implied warranty and consequential damages may not apply to you. This warranty gives you specific legal rights. You may have other rights which vary from state to state. This limited warranty extends to products listed in the company's current price schedule.

Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Speco Technologies . 200 New Highway . Amityville . NY . 11701 . [www.specotech.com](http://www.specotech.com)